

Garant GRIDLINE

**Tool cabinet casing for drawers, 20×20G, Height: 900mm****Order data**

Order number	930525 900
GTIN	4062406065362
Item class	9GK

**Description****Version:**

Tool cabinet casing in 24×24G, suitable for drawers 20×20G. For drawer runner mountings at 25 mm intervals. The casing can be locked centrally with a cylinder lock.

**Suitable for:**

Drawers No. 930533; 930534.

**Colour:**

RAL 7035 light grey **powder coated**.

**Note:**

When fitting out the tool cabinet with drawers, check that the sum of the heights of individual drawer fronts corresponds to the usable height for the cabinet.

**Technical description**

Weight	34 kg
Usable height for drawers	800 mm
Depth	600 mm
Electronic locking system can be retrofitted	yes

Height	900 mm
Number of doors	0
Usable height	800 mm
Width	600 mm
Width in G	24
Depth in G	24
Version	for individual configuration
maximum load capacity	4000 kg
Number of pull-out shelves	0
Number of drawers	0
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	20×20G
Type of product	Tool cabinet body

## Accessories

Lock plate for GridLine Type HU21	914227 HU21
-----------------------------------	-------------