

 GRIDLINE

Roller cabinet with drawers 75 kg, 26×20G, Height mm / number of drawers: 860/5



Order data

Order number	930615 860/5
GTIN	4062406065430
Item class	9GK

Description

Version:

Complete with drawers 26×20G.

Roller cabinet in 30×24G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With anti-roll lip on 4 sides, ribbed rubber mat and 2-component Haptoprene® push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

100% full extension drawers with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport. Absolutely necessary for all roller cabinets.

Components:

Drawer front height, mm: 75, 75, 100, 150, 200

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer/pull-out shelf load capacity: 75 kg

Drawer runner extension (partial/full extension): 100 %

Individual drawer release system: One-hand

Drawer usable area in G: 26×20
 Height: 885 mm
 Width: 750 mm
 Depth: 600 mm
 Usable height: 600 mm
 Drawer body height: 700 mm
 Drawer usable width: 650 mm

Technical description

Width	750 mm
Weight	106 kg
Drawer usable width	650 mm
Depth	600 mm
Usable height	600 mm
Drawer usable area in G	26×20
Number of drawers	5
maximum load capacity	500 kg
Drawer usable width in G	26
Individual drawer release system	One-hand
Drawer usable depth in G	20
Drawer body height	700 mm
Height	885 mm
Drawer runner extension (partial/full extension)	100 %
Drawer front height	75 mm
Drawer front height	75 mm
Drawer front height	100 mm
Drawer front height	150 mm
Drawer front height	200 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer usable depth	500 mm
Material thickness	1.2 mm

Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	26×20G

Accessories

Slotted / plain divider sets Drawer front height / type 100/1	950370 100/1
Slotted / plain divider sets Drawer front height / type 75/1	950370 75/1
easyPick small parts storage bins set Drawer front height / type 75/1	950350 75/1
Set of troughs Drawer front height / type 50/1	950360 50/1
Drawer with one-handed individual drawer release system, 75 kg Drawer front height 200 mm	930634 200
Drawer with one-handed individual drawer release system, 75 kg Drawer front height 150 mm	930634 150
Drawer with one-handed individual drawer release system, 75 kg Drawer front height 100 mm	930634 100
Drawer with one-handed individual drawer release system, 75 kg Drawer front height 75 mm	930634 75