

Garant GRIDLINE

Tool cabinet casing for drawers, 26×20G, Height: 700mm



Order data

Order number	930625 700
GTIN	4062406065454
Item class	9GK

Description

Version:

Tool cabinet casing in 30×24G, suitable for drawers 26×20G. For drawer runner mountings at 25 mm intervals. The casing can be locked centrally with a cylinder lock.

Suitable for:

Drawers No. 930633, 930634, 930635, 930636.

Colour:

RAL 7035 light grey **powder coated**.

Note:

When fitting out the tool cabinet with drawers, check that the sum of the heights of individual drawer fronts corresponds to the usable height for the cabinet.

Technical description

Electronic locking system can be retrofitted	yes
Usable height for drawers	600 mm
Width	750 mm
Depth	600 mm

Usable height	600 mm
Weight	33 kg
Number of doors	0
Height	700 mm
Width in G	30
Depth in G	24
Version	for individual configuration
maximum load capacity	4000 kg
Number of pull-out shelves	0
Number of drawers	0
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	26×20G
Type of product	Tool cabinet body

Accessories

Lock plate for GridLine Type HU21	914227 HU21
-----------------------------------	-------------