

Garant
Socket set 3/8 inch square drive 30 pieces, Type: SD

Order data

Order number	634025 SD
GTIN	4062406060756
Item class	61A

Description
Version:

Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124. Internal / external square drives to **DIN 3120**.

System box of virtually indestructible ABS plastic with integral hinges and snap fastener.

All tools are held securely for easy access in a specially moulded hard-wearing **PUR foam inlay**.

The Surface Drive profile works directly on the faces of the nuts and bolts; weaker corners are protected. Even intermediate sizes (e.g. inch size bolts) and worn bolt heads can be tightened or released using the Surface Drive profile. The Wobble-Fix extensions allow use at an angle and can be secured by clicking into place.

Application:

For hexagon head screws / nuts with thread M5 – M14 and 1/4 – 1/2 inch (American inch sizes), for spark plugs 16 and 20.8 mm and for hexagon socket head screws with thread M5 – M12.

Material:

Chrome vanadium steel, chrome-plated.

Supplied with:

Surface Drive hexagon sockets: 14 pcs. No. 637125 size 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 21; 22

Spark plug sockets: 2 pcs. No. 637329 size 16; 20.8

Screwdriver bits hexagon: 5 pcs. No. 637629 size 4; 5; 6; 8; 10

Screwdriver bits for Torx®: 3 pcs. similar to No. 637560 size TX25; TX30; TX40

T-handle: 1 pc. No. 635729

Extensions "Wobble-Fix": 2 pcs. similar to No. 635635 size 75; 240

Universal joint: 1 pc. No. 636229

Ratchet: 1 pc. No. 635025

Converter: 1 pc. similar to No. 650000 size 3 drive input hexagon 1/4 inch E 6.3 - drive output square 3/8 inch

Presented in: ABS plastic box

Technical description

Width across flats range, Surface Drive	8-22 mm
Width across flats range, hexagon wrenches	4-10 mm
Square drive	3/8 in
Drive profile	Hexagon socket Surfacedrive
Drive profile	Hexagon screwdriver
Drive profile	Screwdriver for TORX® screws
Drive profile	Bi-hex socket
Hexagon socket profile	Surfacedrive
Square with Wobble-Fix	with angle of inclination
Packaging	ABS plastic box
Length	357 mm
Width	176 mm
Height	45 mm
Degree of fill of a drawer in units	6×14
Type of product	Socket spanner

Accessories

Hexagon bit socket, 3/8 inch Hexagon 10 mm	637629 10
Hexagon bit socket, 3/8 inch Hexagon 5 mm	637629 5
Single hexagon socket for spark plugs 3/8 inch Width across flats 16 mm	637329 16
Modular box Type 3A	630305 3A
Hexagon socket, 3/8 inch Surface Drive Width across flats 10 mm	637125 10

Hexagon socket, 3/8 inch Surface Drive Width across flats 14 mm	637125 14
Hexagon socket, 3/8 inch Surface Drive Width across flats 9 mm	637125 9
Hexagon bit socket, 3/8 inch Hexagon 8 mm	637629 8
Hexagon bit socket, 3/8 inch Hexagon 6 mm	637629 6
T-handle, 3/8 inch overall length 200 mm	635729 200
Hexagon socket, 3/8 inch Surface Drive Width across flats 22 mm	637125 22
Hexagon socket, 3/8 inch Surface Drive Width across flats 11 mm	637125 11
Hexagon socket, 3/8 inch Surface Drive Width across flats 21 mm	637125 21
Universal joint, 3/8 inch Type 3/8	636229 3/8
Hexagon socket, 3/8 inch Surface Drive Width across flats 17 mm	637125 17
Hexagon socket, 3/8 inch Surface Drive Width across flats 13 mm	637125 13
PUR foam inlay for set 634025	630304 634025
Hexagon socket, 3/8 inch Surface Drive Width across flats 19 mm	637125 19
Single hexagon socket for spark plugs 3/8 inch Width across flats 20,8 mm	637329 20,8
Reversible ratchet, 3/8 inch with ejector Type	635025
Hexagon socket, 3/8 inch Surface Drive Width across flats 18 mm	637125 18
Hexagon socket, 3/8 inch Surface Drive Width across flats 12 mm	637125 12
Hexagon socket, 3/8 inch Surface Drive Width across flats 15 mm	637125 15
Hexagon socket, 3/8 inch Surface Drive Width across flats 16 mm	637125 16
Hexagon bit socket, 3/8 inch Hexagon 4 mm	637629 4
	637125 8

Hexagon socket, 3/8 inchSurface Drive Width across flats 8
mm
