

**Garant**
**Socket set 3/8 inch square drive 19 pieces, Type: 12**

**Order data**

Order number	633912 12
GTIN	4062406060749
Item class	61A

**Description**
**Version:**

**Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124.** Internal / external square drives to **DIN 3120.**

All tools are held securely for easy access in a specially moulded hard-wearing **PUR foam inlay.** With bi-hexagon sockets No. 637029.

**Application:**

For hexagon head screws / nuts with thread M5 – M14.

**Material:**

Chrome vanadium steel, chrome-plated.

**Supplied with:**

Sockets: 14 pcs. size 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 21; 22 mm

T-handle: 1 pc. No. 635729

Extensions: 2 pcs. No. 635429 size 75; 240

Universal joint: 1 pc. No. 636229

Ratchet: 1 pc. No. 635025

Storage in: ABS plastic box

**Technical description**

Square drive	3/8 in
Width across flats range, bi-hex sockets	8-22 mm
Drive profile	Bi-hex socket

Packaging	ABS plastic box
Length	357 mm
Width	176 mm
Height	45 mm
Degree of fill of a drawer in units	6×14
Type of product	Socket spanner

## Accessories

T-handle, 3/8 inch overall length 200 mm	635729 200
Modular box Type 3A	630305 3A
Reversible ratchet, 3/8 inch with ejector Type	635025
Extension, 3/8 inch overall length 75 mm	635429 75
Universal joint, 3/8 inch Type 3/8	636229 3/8
PUR foam inlay for set 633912	630304 633912
Extension, 3/8 inch overall length 240 mm	635429 240