

Garant
Socket set 3/8 inch square drive 19 pieces, Type: 12

Order data

| | |
|--------------|---------------|
| Order number | 633912 12 |
| GTIN | 4062406060749 |
| Item class | 61A |

Description
Version:

Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124. Internal / external square drives to **DIN 3120.**

All tools are held securely for easy access in a specially moulded hard-wearing **PUR foam inlay.** With bi-hexagon sockets No. 637029.

Application:

For hexagon head screws / nuts with thread M5 – M14.

Material:

Chrome vanadium steel, chrome-plated.

Supplied with:

Sockets: 14 pcs. size 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 21; 22 mm

T-handle: 1 pc. No. 635729

Extensions: 2 pcs. No. 635429 size 75; 240

Universal joint: 1 pc. No. 636229

Ratchet: 1 pc. No. 635025

Storage in: ABS plastic box

Degree of fill of a drawer in units: 6x14

Height: 45 mm

Square drive: 3/8 inch

Width across flats range, bi-hex sockets: 8-22 mm

Technical description

| | |
|--|-----------------|
| Square drive | 3/8 inch |
| Width across flats range, bi-hex sockets | 8-22 mm |
| Drive profile | Bi-hex socket |
| Packaging | ABS plastic box |
| Length | 357 mm |
| Width | 176 mm |
| Height | 45 mm |
| Degree of fill of a drawer in units | 6×14 |
| Type of product | Socket spanner |

Accessories

| | |
|--|---------------|
| T-handle, 3/8 inch overall length 200 mm | 635729 200 |
| Modular box Type 3A | 630305 3A |
| Reversible ratchet, 3/8 inch with ejector Type | 635025 |
| Extension, 3/8 inch overall length 75 mm | 635429 75 |
| Universal joint 3/8 inch Type 3/8 | 636229 3/8 |
| PUR foam inlay for set 633912 | 630304 633912 |
| Extension, 3/8 inch overall length 240 mm | 635429 240 |