

**Garant**
**Socket set 3/8 inch square drive 37 pieces, Type: 12**

**Order data**

Order number	634799 12
GTIN	4062406060787
Item class	61A

**Description**
**Version:**

**Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124.** Internal / external square drives to **DIN 3120**.

All tools are held securely for easy access in a specially moulded hard-wearing **PUR foam inlay**.

**Application:**

For hexagon head screws / nuts with thread M5 – M12, for external Torx® with thread M4 – M12, for socket head screws with thread M5 – M12, for internal Torx® with thread M3 – M8.

**Material:**

Chrome vanadium steel, chrome-plated.

**Supplied with:**

Bi-hexagon sockets: 11 pcs. No. 637029 size 8; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19

Sockets for Torx®: 7 pcs. size E5; E6; E7; E8; E10; E12; E14

Screwdriver sockets, hexagon: 6 pcs. No. 637629 size 4; 5; 6; 7; 8; 10

Screwdriver sockets for Torx®: 8 pcs. size TX9; TX10; TX15; TX20; TX25; TX27; TX30; TX40

T-handle: 1 pc. No. 635729

Extensions: 2 pcs. No. 635429 size 75; 240

Universal joint: 1 pc. No. 636229

Ratchet: 1 pc. No. 635025

Storage in: ABS plastic box

**Note:**

The range offers in addition space for 4 pieces of small parts storage bins No. 951251 size 2x3/1 or 2 pieces of small parts storage bins No. 951251 size 2x6/1 (not included in the scope of supply).

## Technical description

Square drive	3/8 in
Drive profile	Bi-hex socket
Drive profile	Hexagon screwdriver
Drive profile	Screwdriver for TORX® screws
Drive profile	Socket for TORX® screws
Width across flats range, hexagon wrenches	4-10 mm
Width across flats range, bi-hex sockets	8-19 mm
Packaging	ABS plastic box
Length	510 mm
Width	294 mm
Height	61 mm
Degree of fill of a drawer in units	8x20
Type of product	Socket spanner

## Accessories

Bi-hexagon socket, 3/8 inch Width across flats 8 mm	637029 8
Bi-hexagon socket, 3/8 inch Width across flats 19 mm	637029 19
Bi-hexagon socket, 3/8 inch Width across flats 18 mm	637029 18
Hexagon bit socket, 3/8 inch Hexagon 4 mm	637629 4
Modular box Type 4	630305 4
Bi-hexagon socket, 3/8 inch Width across flats 10 mm	637029 10
easyPick small parts storage bins Height 50 mm Width x depth in G / type 2X3/1	951251 2X3/1
Extension, 3/8 inch overall length 75 mm	635429 75
Extension, 3/8 inch overall length 240 mm	635429 240
Bi-hexagon socket, 3/8 inch Width across flats 15 mm	637029 15

Bi-hexagon socket, 3/8 inch Width across flats 14 mm	637029 14
Hexagon bit socket, 3/8 inch Hexagon 6 mm	637629 6
Bi-hexagon socket, 3/8 inch Width across flats 17 mm	637029 17
PUR foam inlay for set 634799	630304 634799
Hexagon bit socket, 3/8 inch Hexagon 8 mm	637629 8
Bi-hexagon socket, 3/8 inch Width across flats 13 mm	637029 13
T-handle, 3/8 inch overall length 200 mm	635729 200
Hexagon bit socket, 3/8 inch Hexagon 5 mm	637629 5
Hexagon bit socket, 3/8 inch Hexagon 7 mm	637629 7
Bi-hexagon socket, 3/8 inch Width across flats 12 mm	637029 12
Bi-hexagon socket, 3/8 inch Width across flats 11 mm	637029 11
Bi-hexagon socket, 3/8 inch Width across flats 16 mm	637029 16
Hexagon bit socket, 3/8 inch Hexagon 10 mm	637629 10
Reversible ratchet, 3/8 inch with ejector Type	635025
Universal joint, 3/8 inch Type 3/8	636229 3/8
Bi-hexagon socket, 3/8 inch Width across flats 9 mm	637029 9