

Garant
Socket set 3/8 inch square drive 19 pieces, Type: 6

Order data

Order number	633912 6
GTIN	4062406060732
Item class	61A

Description
Version:

Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124. Internal / external square drives to **DIN 3120**.

All tools are held securely for easy access in a specially moulded hard-wearing **PUR foam inlay**. With hexagon sockets No. 637229.

Application:

For hexagon head screws / nuts with thread M5 – M14.

Material:

Chrome vanadium steel, chrome-plated.

Supplied with:

Sockets: 14 pcs. size 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 21; 22 mm

T-handle: 1 pc. No. 635729

Extensions: 2 pcs. No. 635429 size 75; 240

Universal joint: 1 pc. No. 636229

Ratchet: 1 pc. No. 635025

Storage in: ABS plastic box

Technical description

Drive profile	Hexagon socket
Width across flats range, hexagon sockets	8-22 mm
Square drive	3/8 in

Packaging	ABS plastic box
Length	357 mm
Width	176 mm
Height	45 mm
Degree of fill of a drawer in units	6×14
Type of product	Socket spanner

Accessories

Modular box Type 3A	630305 3A
Universal joint, 3/8 inch Type 3/8	636229 3/8
PUR foam inlay for set 633912	630304 633912
Extension, 3/8 inch overall length 240 mm	635429 240
T-handle, 3/8 inch overall length 200 mm	635729 200
Reversible ratchet, 3/8 inch with ejector Type	635025
Extension, 3/8 inch overall length 75 mm	635429 75