

Garant**Socket set 1/2 inch square drive 23 pieces, Type: 6****Order data**

Order number	637812 6
GTIN	4062406061333
Item class	61A

Description**Version:**

Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124. Internal / external square drives to **DIN 3120.**

All tools are held securely for easy access in a specially moulded hard-wearing **PUR foam inlay.** With hexagon sockets No. 642229.

Application:

For hexagon head screws / nuts with thread M6 – M22.

Material:

Chrome vanadium steel, chrome-plated.

Supplied with:

Sockets: 17 pcs. size 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 21; 22; 24; 27; 30; 32; 34 mm

T-handle: 1 pcs 641329

Extensions: 3 pcs. No. 641029 size 75; 130; 255

Universal joint: 1 pc. No. 641629

Ratchet: 1 pc. No. 640025

Storage in: ABS plastic box

Note:

The range offers in addition space for 4 pieces of small parts storage bins No. 951251 size 2×3/1 or 2 pieces of small parts storage bins No. 951251 size 2×6/1 (not included in the scope of supply).

Technical description

Square drive	1/2 in
Number of pieces	23
Drive profile	Hexagon socket
Width across flats range, hexagon sockets	10-34 mm
Packaging	ABS plastic box
Length	510 mm
Width	294 mm
Height	61 mm
Degree of fill of a drawer in units	8x20
Type of product	Socket spanner

Accessories

Universal joint, 1/2 inch Type 1/2	641629 1/2
Extension, 1/2 inch overall length 75 mm	641029 75
Modular box Type 4	630305 4
Extension, 1/2 inch overall length 130 mm	641029 130
Extension, 1/2 inch overall length 255 mm	641029 255
easyPick small parts storage bins Height 50 mm Width×depth in G / type 2X3/1	951251 2X3/1
PUR foam inlay for set 637812	630304 637812
T-handle, 1/2 inch overall length 295 mm	641329 295
Reversible ratchet, 1/2 inch with ejector Type	640025