

Garant
Socket set 1/2 inch square drive 29 pieces, Type: 12

Order data

Order number	637912 12
GTIN	4062406061364
Item class	61A

Description
Version:

Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124. Internal / external square drives to **DIN 3120**.

All tools are held securely for easy access in a specially moulded hard-wearing **PUR foam inlay**. With bi-hexagon sockets No. 642129.

Application:

For hexagon head screws / nuts with thread M6 – M22.

Material:

Chrome vanadium steel, chrome-plated.

Supplied with:

Hexagon socket: 23 pcs. size 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 20; 21; 22; 23; 24; 26; 27; 28; 30; 32; 34 mm

T-handle: 1 pc. No. 641329 size 295

Extensions: 3 pcs. No. 641029 size 75; 125; 250

1 each hexagon socket: 1 pc. No. 641629 size 1/2

Ratchet: 1 pc. No. 640025 size 1/2

Presented in: ABS plastic box

Note:

The range offers in addition space for 4 pieces of small parts storage bins No. 951251 size 2x3/1 or 2 pieces of small parts storage bins No. 951251 size 2x6/1 (not included in the scope of supply).

Technical description

Square drive	1/2 in
Width across flats	metric
Drive profile	Bi-hexagon socket
Number of pieces	29
Width across flats range, bi-hex sockets	8-34 mm
Length	510 mm
Width	294 mm
Height	61 mm
Degree of fill of a drawer in units	8x20
Type of product	Socket spanner

Accessories

Extension, 1/2 inch overall length 75 mm	641029 75
Reversible ratchet, 1/2 inch with ejector Type	640025
T-handle, 1/2 inch overall length 295 mm	641329 295
PUR foam inlay for set 637912	630304 637912
easyPick small parts storage bins Height 50 mm Width×depth in G / type 2X3/1	951251 2X3/1
Modular box Type 4	630305 4
Universal joint, 1/2 inch Type 1/2	641629 1/2
Extension, 1/2 inch overall length 130 mm	641029 130
Extension, 1/2 inch overall length 255 mm	641029 255
Modular box Type 4-1	630310 4-1