

Garant**Bi-hexagon socket deep, 1/2 inch, Width across flats: 27mm****Order data**

Order number	642529 27
GTIN	4062406062057
Item class	61A

Description**Version:**

Forged from high quality steel, internally bevelled for easy fitting to bolt heads. Square socket drive with close tolerances for secure fit on the drive attachment. Internal square to **DIN 3120**. **Close tolerance widths across flats** protects nuts and bolt heads. **Thin walls** for access to restricted places. Bi-hex **HT drive** profile protects the corners of nuts and bolt heads.

Standard:**DIN 3124-L****Material:**

Chrome vanadium steel, chrome-plated.

Note:

GARANT and HOLEX bi-hex sockets, long, including are available also in imperial sizes from our eShop (GARANT: No. 642532; HOLEX: No. 642522).

Technical description

Width across flats	27 mm
Length	77 mm
Ø drive output end	36 mm
Square drive	1/2 in
Standard	ISO 2725-1
Standard	DIN EN 3709

Standard	DIN 3124
Standard	ASME B 107.5M
Standard	DIN EN 3710
Drive profile	Bi-hex socket
Material	Chrome vanadium steel
Surface	chrome-plated
with AS Drive profile.	yes
Type of product	Socket insert