

Garant
Bi-hexagon socket deep, 1/2 inch, Width across flats: 14mm

Order data

Order number	642529 14
GTIN	4062406061968
Item class	61A

Description
Version:

Forged from high quality steel, internally bevelled for easy fitting to bolt heads. Square socket drive with close tolerances for secure fit on the drive attachment. Internal square to **DIN 3120**. **Close tolerance widths across flats** protects nuts and bolt heads. **Thin walls** for access to restricted places. Bi-hex **HT drive** profile protects the corners of nuts and bolt heads.

Standard:
DIN 3124-L
Material:

Chrome vanadium steel, chrome-plated.

Note:

GARANT and HOLEX bi-hex sockets, long, including are available also in imperial sizes from our eShop (GARANT: No. 642532; HOLEX: No. 642522).

Technical description

Width across flats	14 mm
Length	77 mm
Ø drive output end	20.4 mm
Square drive	1/2 in
Standard	ISO 2725-1
Standard	DIN EN 3709

Standard	DIN 3124
Standard	ASME B 107.5M
Standard	DIN EN 3710
Drive profile	Bi-hex socket
Material	Chrome vanadium steel
Surface	chrome-plated
with AS Drive profile.	yes
Type of product	Socket insert