

 GRIDLINE

Roller cabinet with drawers 75 kg, 36×20G, Height mm / number of drawers: 860/5



Order data

Order number	930725 860/5
GTIN	4062406062354
Item class	9GK

Description

Version:

Complete with drawers 36×20G.

Roller cabinet in 40×24G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With anti-roll lip on 4 sides, ribbed rubber mat and 2-component Haptoprene® push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

100% full extension drawers with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport. Absolutely necessary for all roller cabinets.

Components:

Drawer front height, mm: 75, 75, 100, 150, 200

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer/pull-out shelf load capacity: 75 kg

Drawer runner extension (partial/full extension): 100 %

Individual drawer release system: One-hand

Drawer usable area in G: 36×20

Height: 885 mm

Width: 1000 mm
 Depth: 600 mm
 Usable height: 600 mm
 Drawer body height: 700 mm
 Drawer usable width: 900 mm

Technical description

Drawer runner extension (partial/full extension)	100 %
Drawer usable depth in G	20
maximum load capacity	450 kg
Usable height	600 mm
Drawer body height	700 mm
Drawer usable width	900 mm
Drawer usable width in G	36
Weight	131 kg
Drawer/pull-out shelf load capacity	75 kg
Individual drawer release system	One-hand
Width	1000 mm
Drawer front height	75 mm
Drawer front height	75 mm
Drawer front height	100 mm
Drawer front height	150 mm
Drawer front height	200 mm
Number of drawers	5
Drawer usable area in G	36×20
Drawer usable depth	500 mm
Wheel Ø	125 mm
Depth	600 mm
Height	885 mm
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock

Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	36×20G

Accessories

easyPick small parts storage bins set Drawer front height / type 75/1	950400 75/1
Slotted / plain divider sets Drawer front height / type 100/1	950420 100/1
Drawer with one-handed individual drawer release system, 75 kg Drawer front height 75 mm	930744 75
Drawer with one-handed individual drawer release system, 75 kg Drawer front height 100 mm	930744 100
Drawer with one-handed individual drawer release system, 75 kg Drawer front height 150 mm	930744 150
Drawer with one-handed individual drawer release system, 75 kg Drawer front height 200 mm	930744 200