

Garant GRIDLINE

**Tool cabinet casing for drawers, 36×20G, Height: 1500mm****Order data**

Order number	930735 1500
GTIN	4062406062385
Item class	9GK

**Description****Version:**

Tool cabinet casing in 40×24G, suitable for drawers 36×20G. For drawer runner mountings at 25 mm intervals. The casing can be locked centrally with a cylinder lock.

**Suitable for:**

Drawers No. 930743, 930744, 930745, 930746.

**Colour:**

RAL 7035 light grey **powder coated**.

**Note:**

When fitting out the tool cabinet with drawers, check that the sum of the heights of individual drawer fronts corresponds to the usable height for the cabinet.

**Technical description**

Usable height for drawers	1400 mm
Usable height	1400 mm
Electronic locking system can be retrofitted	yes
Depth	600 mm

Weight	61 kg
Number of doors	0
Height	1500 mm
Width	1000 mm
Depth in G	24
Width in G	40
Version	for individual configuration
maximum load capacity	4000 kg
Number of pull-out shelves	0
Number of drawers	0
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	36×20G
Type of product	Tool cabinet body

---

## Accessories

Lock plate for GridLine Type HU21	914227 HU21
-----------------------------------	-------------