Garant GRIDUNG

Tool cabinet complete with drawers 75 kg, 20×24G, Height mm / number of drawers: 1000/7



Order data

Order number	931005 1000/7
GTIN	4062406062439
Item class	9GK

Description

NOTE: Colour selection possible

Version:

Completely equipped tool cabinet in 24×28G, with drawers 20×24G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Fitted with:

Drawer front height, mm: 50, 75, 100, 100, 125, 150, 300

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated**. **Drawer body not configurable**, **always RAL 7035 light grey**.

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer usable area in G: 20×24

Height: 1000 mm Width: 600 mm Depth: 700 mm Usable height: 900 mm

Usable height for drawers: 900 mm Drawer usable width: 500 mm

Technical description

Usable height for drawers	900 mm
Drawer usable depth	600 mm
Height	1000 mm
Width	600 mm
Weight	123 kg
Number of drawers	7
Drawer usable area in G	20×24
Electronic locking system can be retrofitted	yes
Drawer usable depth in G	24
Drawer usable width	500 mm
Usable height	900 mm
Drawer front height	50 mm
Drawer front height	75 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	125 mm
Drawer front height	150 mm
Drawer front height	300 mm
Number of doors	0
Depth	700 mm
Drawer usable width in G	20
Number of pull-out shelves	0
Base cabinet underneath height-adjustable workstation	no
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg



Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×24G
Type of product	Tool cabinet

Accessories

Drawer, 75 kg Drawer front height 75 mm	931043 75
Drawer, 75 kg Drawer front height 50 mm	931043 50
Drawer, 75 kg Drawer front height 300 mm	931043 300
Drawer, 75 kg Drawer front height 150 mm	931043 150
Drawer, 75 kg Drawer front height 100 mm	931043 100
Drawer, 75 kg Drawer front height 125 mm	931043 125
Lock plate for GridLine Type HU21	914227 HU21
Tool cabinet casing for drawers Height 1000 mm	931035 1000