

Garant GRIDLINE

Tool cabinet complete with drawers 75 kg, 26×24G, Height mm / number of drawers: 1500/15**Order data**

Order number	931105 1500/15
GTIN	4062406062705
Item class	9GK

Description**Version:**

Completely equipped tool cabinet in 30×28G, with drawers 26×24G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Fitted with:

Drawer front height, mm: 75, 75, 75, 75, 75, 75, 100, 100, 100, 100, 100, 100, 100, 100, 150

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Technical description

Drawer usable width	650 mm
Depth	700 mm

Weight	269 kg
Drawer usable depth	600 mm
Width	750 mm
Usable height for drawers	1400 mm
Drawer usable area in G	26×24
Electronic locking system can be retrofitted	yes
Drawer usable depth in G	24
Usable height	1400 mm
Number of doors	0
Ribbed rubber inlay with anti-roll lip on 3 sides	no
Drawer front height	75 mm
Drawer front height	75 mm
Drawer front height	75 mm
Drawer front height	75 mm
Drawer front height	75 mm
Drawer front height	75 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	150 mm
Number of drawers	15
Height	1500 mm
Drawer usable width in G	26
ComfortClose	no

Number of pull-out shelves	0
Base cabinet underneath height-adjustable workstation	no
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	26x24G
Type of product	Tool cabinet

Accessories

Lock plate for GridLine Type HU21	914227 HU21
Drawer,75 kg Drawer front height 150 mm	931163 150
Drawer,75 kg Drawer front height 75 mm	931163 75
Drawer,75 kg Drawer front height 100 mm	931163 100
Tool cabinet casing for drawers Height 1500 mm	931155 1500