

Garant GRIDLINE

Tool cabinet casing for drawers, 20×24G, Height: 1000mm**Order data**

Order number	931035 1000
GTIN	4062406062507
Item class	9GK

Description**Version:**

Tool cabinet casing in 24×28G, suitable for drawers 20×24G. For drawer runner mountings at 25 mm intervals. The casing can be locked centrally with a cylinder lock.

Suitable for:

Drawers No. 931043, 931045, 931046, 931048.

Colour:

RAL 7035 light grey **powder coated**.

Note:

When fitting out the tool cabinet with drawers, check that the sum of the heights of individual drawer fronts corresponds to the usable height for the cabinet.

Technical description

Usable height for drawers	900 mm
Height	1000 mm
Electronic locking system can be retrofitted	yes
Depth	700 mm

Width	600 mm
Weight	39 kg
Usable height	900 mm
Number of doors	0
Depth in G	28
Width in G	24
Version	for individual configuration
maximum load capacity	4000 kg
Number of pull-out shelves	0
Number of drawers	0
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	20×24G
Type of product	Tool cabinet body

Accessories

Lock plate for GridLine Type HU21	914227 HU21
-----------------------------------	-------------