

Garant GRIDLINE

Tool cabinet complete with drawers 75 kg, 26×24G, Height mm / number of drawers: 1500/9



Order data

Order number	931105 1500/9
GTIN	4062406062682
Item class	9GK

Description

Version:

Completely equipped tool cabinet in 30×28G, with drawers 26×24G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Fitted with:

Drawer front height, mm: 100, 100, 100, 150, 150, 150, 150, 200, 300

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Technical description

Usable height	1400 mm
Drawer usable width in G	26

Ribbed rubber inlay with anti-roll lip on 3 sides	no
ComfortClose	no
Number of doors	0
Drawer usable area in G	26×24
Depth	700 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	150 mm
Drawer front height	150 mm
Drawer front height	150 mm
Drawer front height	150 mm
Drawer front height	200 mm
Drawer front height	300 mm
Drawer usable depth	600 mm
Drawer usable width	650 mm
Drawer usable depth in G	24
Usable height for drawers	1400 mm
Electronic locking system can be retrofitted	yes
Width	750 mm
Number of drawers	9
Height	1500 mm
Weight	205 kg
Number of pull-out shelves	0
Base cabinet underneath height-adjustable workstation	no
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock

Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	26x24G
Type of product	Tool cabinet

Accessories

Drawer,75 kg Drawer front height 300 mm	931163 300
Drawer,75 kg Drawer front height 200 mm	931163 200
Lock plate for GridLine Type HU21	914227 HU21
Drawer,75 kg Drawer front height 150 mm	931163 150
Drawer,75 kg Drawer front height 100 mm	931163 100
Tool cabinet casing for drawers Height 1500 mm	931155 1500