

Garant GRIDLINE

Tool cabinet complete with drawers 75 kg, 26×24G, Height mm / number of drawers: 800/6**Order data**

| | |
|--------------|---------------|
| Order number | 931105 800/6 |
| GTIN | 4062406062521 |
| Item class | 9GK |

Description**Version:**

Completely equipped tool cabinet in 30×28G, with drawers 26×24G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Fitted with:

Drawer front height, mm: 50, 75, 100, 100, 125, 250

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Technical description

| | |
|---|----|
| Drawer usable depth in G | 24 |
| Ribbed rubber inlay with anti-roll lip on 3 sides | no |

| | |
|---|--|
| Electronic locking system can be retrofitted | yes |
| Drawer usable area in G | 26×24 |
| Height | 800 mm |
| Drawer front height | 50 mm |
| Drawer front height | 75 mm |
| Drawer front height | 100 mm |
| Drawer front height | 100 mm |
| Drawer front height | 125 mm |
| Drawer front height | 250 mm |
| Drawer usable width in G | 26 |
| Usable height for drawers | 700 mm |
| Drawer usable depth | 600 mm |
| Number of drawers | 6 |
| Drawer usable width | 650 mm |
| Usable height | 700 mm |
| Weight | 125 kg |
| ComfortClose | no |
| Depth | 700 mm |
| Width | 750 mm |
| Number of doors | 0 |
| Base cabinet underneath height-adjustable workstation | no |
| Number of pull-out shelves | 0 |
| Material thickness | 1.2 mm |
| Drawer/pull-out shelf load capacity | 75 kg |
| Drawer runner extension (partial/full extension) | 100 % |
| Drawer runner extension | Anti-tilt lock |
| Height adjustment interval | 25 mm |
| Cylinder lock | modular lock barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |

| | |
|------------------------|--------------|
| Product name attribute | 26x24G |
| Type of product | Tool cabinet |

Accessories

| | |
|---|-------------|
| Drawer,75 kg Drawer front height 100 mm | 931163 100 |
| Drawer,75 kg Drawer front height 50 mm | 931163 50 |
| Drawer,75 kg Drawer front height 125 mm | 931163 125 |
| Drawer,75 kg Drawer front height 75 mm | 931163 75 |
| Drawer,75 kg Drawer front height 250 mm | 931163 250 |
| Lock plate for GridLine Type HU21 | 914227 HU21 |
| Tool cabinet casing for drawers Height 800 mm | 931155 800 |