

Garant GRIDLINE

Tool cabinet complete with drawers 75 kg, 26×24G, Height mm / number of drawers: 1000/8



Order data

Order number	931105 1000/8
GTIN	4062406062590
Item class	9GK

Description

Version:

Completely equipped tool cabinet in 30×28G, with drawers 26×24G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Fitted with:

Drawer front height, mm: 75, 75, 100, 100, 100, 150, 150, 150

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Technical description

Drawer usable width in G	26
Height	1000 mm

Drawer usable area in G	26x24
Weight	162 kg
Drawer usable depth	600 mm
Usable height	900 mm
ComfortClose	no
Electronic locking system can be retrofitted	yes
Number of doors	0
Ribbed rubber inlay with anti-roll lip on 3 sides	no
Width	750 mm
Usable height for drawers	900 mm
Depth	700 mm
Number of drawers	8
Drawer usable width	650 mm
Drawer usable depth in G	24
Drawer front height	75 mm
Drawer front height	75 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	150 mm
Drawer front height	150 mm
Drawer front height	150 mm
Base cabinet underneath height-adjustable workstation	no
Number of pull-out shelves	0
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm

Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	26x24G
Type of product	Tool cabinet

Accessories

Drawer,75 kg Drawer front height 100 mm	931163 100
Drawer,75 kg Drawer front height 150 mm	931163 150
Drawer,75 kg Drawer front height 75 mm	931163 75
Lock plate for GridLine Type HU21	914227 HU21
Tool cabinet casing for drawers Height 1000 mm	931155 1000