

**Garant**
**Lever lock toolholder, left-hand, Shank / insert size: 40/19mm**

**Order data**

Order number	251107 40/19
GTIN	4062406060862
Item class	21T

**Technical description**

Overall length L	250 mm
Functional width L <sub>4</sub>	35 mm
Shim pins pack	259044 1
Lever screw	259018 1
Shim	259031 16
Lever	259015 1
ISO code toolholder	PSBNR/L 4040S19
Shim punches pack	259047 1
Shank size	40 mm
Insert size	19 mm
suitable indexable insert	SN.. 1906..
Series	QuickTurn
Head length L <sub>1</sub>	48 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle $\kappa$	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar