

Garant GRIDLINE

Tool cabinet complete with drawers 200 kg, 26×24G, Height mm / number of drawers: 800/6A**Order data**

Order number	931115 800/6A
GTIN	4062406062736
Item class	9GK

Description**Version:**

Completely equipped tool cabinet in 30×28G, with drawers 26×24G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Drawers **50 mm with 75 kg** load capacity. Drawers **from 75 mm with 200 kg** load capacity.

Fitted with:

Drawer front height, mm: 75, 75, 100, 100, 150, 200

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Technical description

Usable height	700 mm
---------------	--------

Drawer usable width	650 mm
Drawer usable depth	600 mm
Number of drawers	6
Electronic locking system can be retrofitted	yes
Drawer usable area in G	26×24
Drawer front height	75 mm
Drawer front height	75 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	150 mm
Drawer front height	200 mm
Drawer usable width in G	26
Depth	700 mm
Height	800 mm
Drawer usable depth in G	24
Number of doors	0
ComfortClose	no
Width	750 mm
Usable height for drawers	700 mm
Weight	127 kg
Ribbed rubber inlay with anti-roll lip on 3 sides	no
Base cabinet underneath height-adjustable workstation	no
Number of pull-out shelves	0
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	200 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel

Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	26x24G
Type of product	Tool cabinet

Accessories

Drawer,200 kg Drawer front height 100 mm	931165 100
Drawer,200 kg Drawer front height 150 mm	931165 150
Lock plate for GridLine Type HU21	914227 HU21
Drawer,200 kg Drawer front height 200 mm	931165 200
Drawer,200 kg Drawer front height 75 mm	931165 75
Tool cabinet casing for drawers Height 800 mm	931155 800