

Garant
Lever lock toolholder, left-hand, Shank / insert size: 40/19mm

Order data

Order number	251113 40/19
GTIN	4062406063184
Item class	21T

Technical description

Shim punches pack	259047 1
Functional width L ₄	50 mm
ISO code toolholder	PSSNR/L 4040S19
suitable indexable insert	SN.. 1906..
Head length L ₁	45 mm
Series	QuickTurn
Insert size	19 mm
Shim	259031 16
Lever screw	259018 1
Shim pins pack	259044 1
Shank size	40 mm
Lever	259015 1
Overall length L	250 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no

Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar