

Garant GRIDLINE

Tool cabinet casing for drawers, 36×24G, Height: 800mm**Order data**

Order number	931335 800
GTIN	4062406063702
Item class	9GK

Description**Version:**

Tool cabinet casing in 40×28G, suitable for drawers 36×24G. For drawer runner mountings at 25 mm intervals. The casing can be locked centrally with a cylinder lock.

Suitable for:

Drawers No. 931353, 931354, 931355, 931356.

Colour:

RAL 7035 light grey **powder coated**.

Note:

When fitting out the tool cabinet with drawers, check that the sum of the heights of individual drawer fronts corresponds to the usable height for the cabinet.

Technical description

Depth	700 mm
Weight	45 kg
Number of doors	0
Electronic locking system can be retrofitted	yes

Usable height for drawers	700 mm
Height	800 mm
Usable height	700 mm
Width	1000 mm
Width in G	40
Depth in G	28
Version	for individual configuration
maximum load capacity	4000 kg
Number of pull-out shelves	0
Number of drawers	0
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	36×24G
Type of product	Tool cabinet body

Accessories

Lock plate for GridLine Type HU21	914227 HU21
-----------------------------------	-------------