


Garant GRIDLINE

Drawer, 75 kg, 36×24G, Drawer front height: 150mm**Order data**

Order number	931353 150
GTIN	4062406063788
Item class	9GK

Description**Version:**

100% full extension drawers with differential runners. Aluminium handle with labelling strips that can be exchanged and rewritten.

Slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

Load capacity 75 kg.

Suitable for:

Tool cabinet casing 40×28G No. 931335.

Supplied with:

Drawers each complete with 1 pair drawer runner rails.

Colour:

Drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Drawer/pull-out shelf load capacity	75 kg
Weight	20 kg
Usable height	125 mm
Front height	150 mm
Drawer usable area in G	36×24
Usable depth in G	24
Usable width in G	36

Application range	Tool cabinet
Usable width	900 mm
Usable depth	600 mm
with individual drawer release system	no
Material thickness	1.2 mm
Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	36×24G
Type of product	Drawer

Accessories

Labelling strip set 10 pieces Drawer usable width in G 36	951030 36
Pack of PVC covers for handles 10 pieces Drawer usable width in G 36	951032 36
Handle end caps 20 pieces Type 10	951025 10