

Garant GRIDLINE

**Drawer, 75 kg, 20×20G, Drawer front height: 125mm****Order data**

Order number	930533 125
GTIN	4062406063924
Item class	9GK

**Description****Version:**

**100% full extension drawers** with differential runners. Aluminium handle with labelling strips that can be exchanged and rewritten.

Slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

**Suitable for:**

Tool cabinet casing 24×24G No. 930525.

**Supplied with:**

Drawers each complete with 1 pair drawer runner rails.

**Colour:**

Drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Technical description**

Drawer usable area in G	20×20
Weight	10 kg
Front height	125 mm
Drawer/pull-out shelf load capacity	75 kg
Usable height	100 mm
Usable width in G	20
Usable depth in G	20

Application range	Tool cabinet
Usable depth	500 mm
Usable width	500 mm
with individual drawer release system	no
Material thickness	1.2 mm
Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	20×20G
Type of product	Drawer

---

## Accessories

Pack of PVC covers for handles 10 pieces Drawer usable width in G 20	951032 20
Labelling strip set 10 pieces Drawer usable width in G 20	951030 20
Handle end caps 20 pieces Type 10	951025 10