

Garant

**Indexable face mill 45° right-hand cutting, with bore, \varnothing D / number of teeth Z:
160/7mm**


Order data

Order number	214200 160/7
GTIN	4045197702364
Item class	210

Description
Version:

For arbors to DIN 2079, with 4 additional attachment holes.

Note:

Use GARANT torque screwdriver TQ No. **211750 size 5.7** with bit shank No. **674252 size 20IP**.
For technical reasons **without internal coolant supply**.

Technical description

suitable indexable insert	SE.. 1204..
Mounting bore \varnothing	40 mm
Pack of insert screws	219800 (20IP; 5.7 Nm)
Overall length L_{tot}	63 mm
Cutting edge $\varnothing D_c$	160 mm
maximum external $\varnothing D_{max}$	173 mm

Number of cutting edges Z	7
Shank type	with bore
Setting angle κ	45 degrees
Spacing of the cutters	unequal spacing
Through-coolant	yes
Machining strategy	MTC
Tool exchange	PowerCard
Type of product	Face mill

Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 20IP	674252 20IP
Torque screwdriver, fixed setting set torque 5,7 N·m	211750 5,7
Set of insert screws 10 pieces	219800