


Garant GRIDLINE

## Drawer, 200 kg, 56×24G, Drawer front height: 150mm



### Order data

Order number	931555 150
GTIN	4062406065065
Item class	9GK

### Description

#### Version:

**100% full extension drawers** with differential runners. Aluminium handle with labelling strips that can be exchanged and rewritten.

Slots at 50-mm/2G intervals to take slotted dividers (from drawer front height 75 mm).

Load capacity 200 kg.

#### Suitable for:

Tool cabinet casing 56×24G No. 931535.

#### Supplied with:

Drawers each complete with 1 pair drawer runner rails.

#### Colour:

Drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

#### Note:

Only GridLine divider inserts can be used in the widths 2G, 4G, 6G, 8G, 10G or 12 G.

### Technical description

Front height	150 mm
Drawer usable area in G	56×24
Usable height	125 mm
Weight	26 kg
Drawer/pull-out shelf load capacity	200 kg
Usable width in G	56
Usable depth in G	24

Application range	Tool cabinet
Usable width	1400 mm
Usable depth	600 mm
with individual drawer release system	no
Material thickness	1.2 mm
Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	56×24G
Type of product	Drawer

---

## Accessories

Labelling strip set 10 pieces Drawer usable width in G 56	951030 56
Handle end caps 20 pieces Type 10	951025 10
Pack of PVC covers for handles 10 pieces Drawer usable width in G 56	951032 56