

bimos

## Sitting-standing stool, PU foam with glides



### Order data

Order number	965421
GTIN	4016849432885
Item class	96B

### Description

#### Version:

Aluminium **five-point star base (Ø 600 mm)**. Continuous height adjustment by **gas pressure spring**. Seat of SoftTouch PU foam with ribbed profile. **Soft seat with non-slip surface**, ribbed profile allows air circulation (climate comfort). **Ergonomic backrest** (height 190mm) supports correct posture. PU foam, soft, comfortable, washable.

#### Application:

Ideal combination of standing and sitting. For use at sitting or standing workstations, or a combination of both.

Standing stool with glides – for a working height of 720 – 1000 mm.

#### Standard:

##### DIN 68877

Load capacity chair: 120 kg

Height adjustment range: 510 - 780 mm

Seat width: 340 mm

Seat depth: 300 mm

Colour of seat material: black

### Technical description

Material of base	Polished aluminium
with backrest	yes
Seat width	340 mm
Star base Ø	580 mm
Height adjustment version	Gas pressure spring
Base version	Glides
Material of seat surface	PU foam
Seat depth	300 mm
Support frame version	5-point star base
Colour of seat material	black
Standard	DIN 68877
Backrest height	190 mm
Seat tilt adjustment	no
Type of height adjustment	Height adjustment lever
Load capacity chair	120 kg
Height adjustment range	510 - 780 mm
Type of product	Standing stool

---

## Accessories

Glides (1 set = 5 pieces)	963188
---------------------------	--------