

Garant GRIDLINE

**Tool cabinet complete with drawers 75 kg, 36×20G, Height mm / number of drawers: 1500/9****Order data**

Order number	930705 1500/9
GTIN	4062406065621
Item class	9GK

**Description****Version:**

Completely equipped tool cabinet in 40×24G, with drawers 36×20G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

**Fitted with:**

Drawer front height, mm: 100, 100, 100, 100, 150, 150, 200, 250, 250

**Colour:**

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

**Technical description**

Number of drawers	9
Number of doors	0

Usable height	1400 mm
Drawer usable depth	500 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	150 mm
Drawer front height	150 mm
Drawer front height	200 mm
Drawer front height	250 mm
Drawer front height	250 mm
Depth	600 mm
Usable height for drawers	1400 mm
Weight	224 kg
Electronic locking system can be retrofitted	yes
Height	1500 mm
Drawer usable width	900 mm
Width	1000 mm
Drawer usable area in G	36×20
Drawer usable depth in G	20
Drawer usable width in G	36
Base cabinet underneath height-adjustable workstation	no
Number of pull-out shelves	0
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel

Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	36x20G
Type of product	Tool cabinet

---

## Accessories

Drawer,75 kg Drawer front height 150 mm	930743 150
Lock plate for GridLine Type HU21	914227 HU21
Tool cabinet casing for drawers Height 1500 mm	930735 1500
Drawer,75 kg Drawer front height 100 mm	930743 100
Drawer,75 kg Drawer front height 200 mm	930743 200
Drawer,75 kg Drawer front height 250 mm	930743 250