

Garant GRIDLINE

## Tool cabinet complete with drawers 200 kg, 36×20G, Height mm / number of drawers: 1500/11



### Order data

Order number	930715 1500/11
GTIN	4062406065706
Item class	9GK

### Description

#### NOTE: Colour selection possible

#### Version:

Completely equipped tool cabinet in 40×24G, with drawers 36×20G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Drawers **50 mm with 75 kg** load capacity. Drawers **from 75 mm with 200 kg** load capacity.

#### Fitted with:

Drawer front height, mm: 50, 75, 100, 100, 100, 100, 125, 150, 150, 200, 250

#### Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

#### Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Drawer usable area in G: 36×20

Height: 1500 mm

Width: 1000 mm

Depth: 600 mm  
 Usable height: 1400 mm  
 Usable height for drawers: 1400 mm  
 Drawer usable width: 900 mm

## Technical description

Width	1000 mm
Electronic locking system can be retrofitted	yes
Drawer usable width	900 mm
Drawer front height	50 mm
Drawer front height	75 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	125 mm
Drawer front height	150 mm
Drawer front height	150 mm
Drawer front height	200 mm
Drawer front height	250 mm
Drawer usable depth	500 mm
Usable height for drawers	1400 mm
Usable height	1400 mm
Weight	246 kg
Height	1500 mm
Number of drawers	11
Depth	600 mm
Number of doors	0
Drawer usable area in G	36×20
Drawer usable width in G	36

Drawer usable depth in G	20
Base cabinet underneath height-adjustable workstation	no
Number of pull-out shelves	0
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	200 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	36x20G
Type of product	Tool cabinet

## Accessories

Lock plate for GridLine Type HU21	914227 HU21
Drawer, 200 kg Drawer front height 100 mm	930745 100
Drawer, 200 kg Drawer front height 75 mm	930745 75
Drawer, 200 kg Drawer front height 250 mm	930745 250
Drawer, 200 kg Drawer front height 200 mm	930745 200
Drawer, 200 kg Drawer front height 150 mm	930745 150
Drawer, 200 kg Drawer front height 125 mm	930745 125
Tool cabinet casing for drawers Height 1500 mm	930735 1500
Drawer, 75 kg Drawer front height 50 mm	930743 50