

Garant GRIDLINE

Tool cabinet complete with drawers 200 kg, 46×24G, Height mm / number of drawers: 800/6



Order data

Order number	931415 800/6
GTIN	4062406065737
Item class	9GK

Description

Version:

Completely equipped tool cabinet in 50×28G, with drawers 46×24G. Cabinet can be centrally locked by a cylinder lock. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 50-mm/2G intervals (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time. Drawers **50 mm with 75 kg** load capacity. Drawers **from 75 mm with 200 kg** load capacity.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Only GridLine divider inserts can be used in the widths 2G, 4G, 6G, 8G, 10G or 12 G.

Technical description

Drawer usable width in G	46
Number of doors	0
Drawer usable depth	600 mm
Weight	179 kg

Drawer usable depth in G	24
Electronic locking system can be retrofitted	yes
Number of drawers	6
Width	1250 mm
Height	800 mm
Depth	700 mm
Usable height for drawers	700 mm
Drawer usable area in G	46x24
Usable height	700 mm
Drawer usable width	1150 mm
Drawer front height	75 mm
Drawer front height	75 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	100 mm
Drawer front height	250 mm
Number of pull-out shelves	0
Base cabinet underneath height-adjustable workstation	no
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	200 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	46x24G
Type of product	Tool cabinet

Accessories

Drawer,200 kg Drawer front height 300 mm	931455 300
Drawer,200 kg Drawer front height 75 mm	931455 75
Drawer,200 kg Drawer front height 150 mm	931455 150
Drawer,200 kg Drawer front height 250 mm	931455 250
Drawer,200 kg Drawer front height 100 mm	931455 100
Drawer,200 kg Drawer front height 200 mm	931455 200
Lock plate for GridLine Type HU21	914227 HU21
Drawer,200 kg Drawer front height 125 mm	931455 125
Tool cabinet casing for drawers Height 800 mm	931435 800