

Garant GRIDLINE

Tool cabinet complete with drawers 200 kg, 56×24G, Height mm / number of drawers: 1000/7



Order data

Order number	931505 1000/7
GTIN	4062406066185
Item class	9GK

Description

Version:

Completely equipped tool cabinet in 60×28G, with drawers 56×24G. Cabinet can be centrally locked by a cylinder lock. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 50-mm/2G intervals (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Only GridLine divider inserts can be used in the widths 2G, 4G, 6G, 8G, 10G or 12 G.

Technical description

Drawer front height	75 mm
Drawer front height	75 mm
Drawer front height	125 mm
Drawer front height	125 mm

Drawer front height	150 mm
Drawer front height	150 mm
Drawer front height	200 mm
Drawer usable depth in G	24
Drawer usable width in G	56
Number of doors	0
Height	1000 mm
Drawer usable width	1400 mm
Usable height	900 mm
Usable height for drawers	900 mm
Width	1500 mm
Drawer usable area in G	56×24
Electronic locking system can be retrofitted	yes
Depth	700 mm
Weight	242 kg
Drawer usable depth	600 mm
Number of drawers	7
Base cabinet underneath height-adjustable workstation	no
Number of pull-out shelves	0
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	200 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	56×24G
Type of product	Tool cabinet

Accessories

Drawer,200 kg Drawer front height 150 mm	931555 150
Drawer,200 kg Drawer front height 125 mm	931555 125
Drawer,200 kg Drawer front height 250 mm	931555 250
Drawer,200 kg Drawer front height 75 mm	931555 75
Drawer,200 kg Drawer front height 200 mm	931555 200
Drawer,200 kg Drawer front height 100 mm	931555 100
Drawer,200 kg Drawer front height 300 mm	931555 300
Lock plate for GridLine Type HU21	914227 HU21
Tool cabinet casing for drawers Height 1000 mm	931535 1000