

Garant GRIDLINE

Tool cabinet complete with drawers 200 kg, 56×24G, Height mm / number of drawers: 1250/9**Order data**

| | |
|--------------|---------------|
| Order number | 931505 1250/9 |
| GTIN | 4062406066215 |
| Item class | 9GK |

Description**Version:**

Completely equipped tool cabinet in 60×28G, with drawers 56×24G. Cabinet can be centrally locked by a cylinder lock. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 50-mm/2G intervals (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Only GridLine divider inserts can be used in the widths 2G, 4G, 6G, 8G, 10G or 12 G.

Technical description

| | |
|-----------------|---------|
| Depth | 700 mm |
| Width | 1500 mm |
| Number of doors | 0 |

| | |
|---|--|
| Number of drawers | 9 |
| Drawer usable width in G | 56 |
| Drawer front height | 75 mm |
| Drawer front height | 75 mm |
| Drawer front height | 100 mm |
| Drawer front height | 100 mm |
| Drawer front height | 125 mm |
| Drawer front height | 125 mm |
| Drawer front height | 150 mm |
| Drawer front height | 200 mm |
| Drawer front height | 200 mm |
| Height | 1250 mm |
| Drawer usable area in G | 56×24 |
| Weight | 308 kg |
| Electronic locking system can be retrofitted | yes |
| Usable height for drawers | 1150 mm |
| Usable height | 1150 mm |
| Drawer usable depth | 600 mm |
| Drawer usable depth in G | 24 |
| Drawer usable width | 1400 mm |
| Base cabinet underneath height-adjustable workstation | no |
| Number of pull-out shelves | 0 |
| Material thickness | 1.2 mm |
| Drawer/pull-out shelf load capacity | 200 kg |
| Drawer runner extension (partial/full extension) | 100 % |
| Drawer runner extension | Anti-tilt lock |
| Height adjustment interval | 25 mm |
| Cylinder lock | modular lock barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |

| | |
|------------------------|--------------|
| Product name attribute | 56x24G |
| Type of product | Tool cabinet |

Accessories

| | |
|--|-------------|
| Drawer,200 kg Drawer front height 100 mm | 931555 100 |
| Drawer,200 kg Drawer front height 250 mm | 931555 250 |
| Drawer,200 kg Drawer front height 150 mm | 931555 150 |
| Drawer,200 kg Drawer front height 125 mm | 931555 125 |
| Drawer,200 kg Drawer front height 300 mm | 931555 300 |
| Drawer,200 kg Drawer front height 200 mm | 931555 200 |
| Lock plate for GridLine Type HU21 | 914227 HU21 |
| Drawer,200 kg Drawer front height 75 mm | 931555 75 |
| Tool cabinet casing for drawers Height 1250 mm | 931535 1250 |