

Garant GRIDLINE

**Tool cabinet casing for drawers, 56×24G, Height: 1250mm****Order data**

Order number	931535 1250
GTIN	4062406066246
Item class	9GK

**Description****Version:**

Tool cabinet casing in 60×28G, suitable for drawers 56×24G. For drawer runner mountings at 25 mm intervals. The casing can be locked centrally with a cylinder lock.

**Suitable for:**

Drawers No. 931555; 931556.

**Colour:**

RAL 7035 light grey **powder coated**.

**Note:**

When fitting out the tool cabinet with drawers, check that the sum of the heights of individual drawer fronts corresponds to the usable height for the cabinet.

**Technical description**

Usable height for drawers	1150 mm
Depth in G	28
Number of doors	0
Weight	84 kg
Width	1500 mm
Depth	700 mm

Usable height	1150 mm
Width in G	60
Height	1250 mm
Version	for individual configuration
maximum load capacity	4000 kg
Number of drawers	0
Number of pull-out shelves	0
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	56×24G
Type of product	Tool cabinet body

---

## Accessories

Lock plate for GridLine Type HU21	914227 HU21
-----------------------------------	-------------