

Garant GRIDLINE

Tool cabinet casing for drawers, 56×24G, Height: 1000mm**Order data**

| | |
|--------------|---------------|
| Order number | 931535 1000 |
| GTIN | 4062406066239 |
| Item class | 9GK |

Description**Version:**

Tool cabinet casing in 60×28G, suitable for drawers 56×24G. For drawer runner mountings at 25 mm intervals. The casing can be locked centrally with a cylinder lock.

Suitable for:

Drawers No. 931555; 931556.

Colour:

RAL 7035 light grey **powder coated**.

Note:

When fitting out the tool cabinet with drawers, check that the sum of the heights of individual drawer fronts corresponds to the usable height for the cabinet.

Technical description

| | |
|---------------|---------|
| Height | 1000 mm |
| Width | 1500 mm |
| Width in G | 60 |
| Usable height | 900 mm |
| Weight | 67 kg |
| Depth | 700 mm |

| | |
|---|---|
| Depth in G | 28 |
| Usable height for drawers | 900 mm |
| Number of doors | 0 |
| Version | for individual configuration |
| maximum load capacity | 4000 kg |
| Number of drawers | 0 |
| Number of pull-out shelves | 0 |
| Material thickness | 1.2 mm |
| Drawer runner extension | Anti-tilt lock |
| Height adjustment interval | 25 mm |
| Cylinder lock | modular lock barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Drawer usable width × usable depth in G | 56×24G |
| Type of product | Tool cabinet body |

Accessories

| | |
|-----------------------------------|-------------|
| Lock plate for GridLine Type HU21 | 914227 HU21 |
|-----------------------------------|-------------|