

**Garant**
**Boring bar carbide, left-hand, Shank  $\varnothing$  / insert size: 0408/04mm**

**Order data**

Order number	260319 0408/04
GTIN	4062406066710
Item class	21T

**Technical description**

Insert size	4 mm
Pack of insert screws	269028 26
Neck width $L_4$	4 mm
Clamping height $L_2$	7.5 mm
Minimum pre-drill $\varnothing D_{\min}$	5.6 mm
Head length $L_1$	26 mm
Centre offset $L_3$	3 mm
ISO code toolholder	E0408F SDUCR/L04
suitable indexable insert	DC.. 04T0..
Overall length $L$	80 mm
Setting angle $\kappa$	93 degrees
Usable depth $T$	1.5 mm
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX5	674248 TX5
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500