

Garant
Boring bar carbide, right-hand, Shank \varnothing / insert size: 0408/04mm

Order data

Order number	260320 0408/04
GTIN	4062406066727
Item class	21T

Technical description

ISO code toolholder	E0408F SDQCR/L04
Overall length L	80 mm
suitable indexable insert	DC.. 04T0..
Clamping height L ₂	7.5 mm
Pack of insert screws	269028 26
Neck width L ₄	4 mm
Setting angle κ	107.5 degrees
Centre offset L ₃	3 mm
Head length L ₁	26 mm
Insert size	4 mm
Minimum pre-drill $\varnothing D_{\min}$	5.6 mm
Usable depth T	1.1 mm
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX5	674248 TX5
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500