

Garant
Boring bar, steel, left-hand, Shank \varnothing / insert size: 10/04mm

Order data

Order number	260345 10/04
GTIN	4062406066772
Item class	21T

Technical description

Overall length L	100 mm
Minimum pre-drill $\varnothing D_{\min}$	12.5 mm
Clamping height L_2	9 mm
Insert size	4 mm
Setting angle κ	93 degrees
suitable indexable insert	DC.. 04T0..
Head length L_1	22 mm
ISO code toolholder	A10H SDXCR/L04
Centre offset L_3	7 mm
Pack of insert screws	269028 26
Usable depth T	5 mm
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX5

674248 TX5

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500