

**Garant**
**Boring bar, steel, right-hand, Shank  $\varnothing$  / insert size: 0408/04mm**

**Order data**

Order number	260340 0408/04
GTIN	4062406066789
Item class	21T

**Technical description**

ISO code toolholder	A0408F SDQCR/L04
Centre offset $L_3$	2.6 mm
Neck width $L_4$	4 mm
Pack of insert screws	269028 26
Insert size	4 mm
Minimum pre-drill $\varnothing D_{\min}$	5.2 mm
Overall length L	80 mm
Setting angle $\kappa$	107.5 degrees
Clamping height $L_2$	7.5 mm
Head length $L_1$	15 mm
suitable indexable insert	DC.. 04T0..
Usable depth T	1.1 mm
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX5	674248 TX5
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500