

Garant
Boring bar steel, right-hand, Shank Ø / insert size: 0408/04mm


Order data

Order number	260342 0408/04
GTIN	4062406066802
Item class	21T

Technical description

Minimum pre-drill Ø D_{min}	5.2 mm
Neck width L_4	4 mm
Centre offset L_3	3 mm
suitable indexable insert	DC.. 04T0..
Clamping height L_2	7.5 mm
Overall length L	80 mm
ISO code toolholder	A0408F SDUCR/L04
Head length L_1	15 mm
Setting angle κ	93 degrees
Pack of insert screws	269028 26
Insert size	4 mm
Usable depth T	1.5 mm
Shank Ø D_s	8 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX5	674248 TX5
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500