

Garant
Boring bar steel, left-hand, Shank \varnothing / insert size: 0408/04mm


Order data

Order number	260343 0408/04
GTIN	4062406066819
Item class	21T

Technical description

Overall length L	80 mm
Neck width L ₄	4 mm
ISO code toolholder	A0408F SDUCR/L04
suitable indexable insert	DC.. 04T0..
Pack of insert screws	269028 26
Head length L ₁	15 mm
Centre offset L ₃	3 mm
Setting angle κ	93 degrees
Insert size	4 mm
Clamping height L ₂	7.5 mm
Minimum pre-drill $\varnothing D_{\min}$	5.2 mm
Usable depth T	1.5 mm
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX5	674248 TX5
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500