



## Angle drill, Type: 720551



### Order data

Order number	075120 720551
GTIN	4014586878843
Item class	03F

### Description

#### Version:

#### FEIN angle drill –

- Gearbox only 96 mm high including drill chuck, width across the head 17 mm.
- Integral switch with clockwise / anticlockwise switch for ease of use.
- Hollow shaft taper arbor for precise concentricity.
- Compact drill for working in places difficult to access.
- Electronic steplessly adjustable speed control for a gentle start to drilling.

#### Advantage:

For working in hard to reach spots.

#### Supplied with:

1 special rim gear drill chuck 0.8 – 10 mm.

#### Note:

Suitable jobber drills can be found from No. 114000.

Manufacturer's designation: WBP10

Power consumption: 500 W

maximum speed: 0 - 1830 min<sup>-1</sup>

Drill chuck adapter: B10

Chuck clamping range: 0.8 - 10 mm

Maximum twist drill size Ø in steel 1st speed: 10 mm

## Technical description

Weight	1.5 kg
maximum vibration to EN	< 2.5 m/s <sup>2</sup>
Manufacturer's designation	WBP10
Chuck clamping range	0.8 - 10 mm
Drill chuck adapter	B10
Power consumption	500 W
maximum speed	0 - 1830 min <sup>-1</sup>
Maximum twist drill size Ø in steel 1st speed	10 mm
maximum twist drill size Ø in wood 1st speed	25 mm
Power supply	Mains operated
Suitable for material	Steel
Type of product	Drill