

**Garant**
**Face mill arbor with cooling channel bores, PSC 63 A = 65, Spigot  $\varnothing$  d<sub>1</sub>: 16mm**

**Order data**

Order number	308547 16
GTIN	4045197703712
Item class	31C

**Description**
**Version:**

- With RFID/Balluffchip bore.
- All shanks hard turned (for smooth running!).
- Mating faces of the PSC internal contour machined.

**Application:**

For holding shell end mills and face mills with cross keyway.

**Supplied with:**

Lock screw.

**Optional extras:**

Toggle spanner No. 309840, cutter lock screw No. 309860.

Coolant tube and assembling key for coolant tubes No. 309885; 309893.

**Technical description**

Overhang dimension A	65 mm
Spare milling cutter lock screw No. 309860 / 309861	16
Suitable toggle spanner No. 309840	16
Spigot $\varnothing$ d <sub>1</sub>	16 mm
External $\varnothing$ D	38 mm
Clamping $\varnothing$ D <sub>1</sub>	16 mm

Adapter	PSC 63 A = 65
Arbor standard	ISO 26623-1
Cooling channel bore	pluggable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 6 μm
Machining strategy	HPC
Type of product	Milling head arbor

---

## Accessories

Toggle spanner for mandrel Ø 16 mm	309840 16
------------------------------------	-----------