

Garant

Face mill arbor with cooling channel bores, PSC 63 A = 65, Spigot \varnothing d₁: 32mm


Order data

Order number	308547 32
GTIN	4045197703743
Item class	31C

Description
Version:

- **With RFID/Balluffchip bore.**
- **All shanks hard turned (for smooth running!).**
- **Mating faces of the PSC internal contour machined.**

Application:

For holding shell end mills and face mills with cross keyway.

Supplied with:

Lock screw.

Optional extras:

Toggle spanner No. 309840, cutter lock screw No. 309860.

Coolant tube and assembling key for coolant tubes No. 309885; 309893.

Technical description

Overhang dimension A	65 mm
Spare milling cutter lock screw No. 309860 / 309861	32
Suitable toggle spanner No. 309840	32
Spigot \varnothing d ₁	32 mm
External \varnothing D	63 mm
Clamping \varnothing D ₁	32 mm

Adapter	PSC 63 A = 65
Arbor standard	ISO 26623-1
Cooling channel bore	pluggable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 6 μm
Machining strategy	HPC
Type of product	Milling head arbor

Accessories

Toggle spanner for mandrel Ø 32 mm	309840 32
------------------------------------	-----------