

Standing stool, height adjustable, Gas pressure spring



Order data

Order number	965631
GTIN	2050000981364
Item class	96B

Description

Version:

Tubular steel frame with anti-slip, oil-resistant glides. Seat height adjustable by locking lever.

Seat of PU foam. Adjustable seat angle and pivotable to either side with automatic return adjustment.

Height adjustment of the seat by **gas pressure safety spring**.

Standard:

DIN 68877

Colour:

Black RAL 9005.

Load capacity chair: 120 kg

Height adjustment range: 645 - 825 mm

Seat width: 320 mm

Seat depth: 220 mm

Colour of seat material: black

Technical description

Colour of seat material	black
Seat width	320 mm

Height adjustment version	Gas pressure spring
Standard	DIN 68877
Support frame version	Base frame
Seat depth	220 mm
Material of base	Steel
Material of seat surface	PU foam
Seat tilt adjustment	yes
Type of height adjustment	Height adjustment lever
Load capacity chair	120 kg
Footprint width	650 mm
Footprint depth	450 mm
Height adjustment range	645 - 825 mm
Type of product	Standing stool

Accessories

Seat for standing stool Type S	963901 S
--------------------------------	----------