

Garant GRIDLINE

Base cabinet with Viewing window swing doors, Height: 750mm**Order data**

Order number	940003 750
GTIN	4062406067052
Item class	9GI

Description**Version:**

Equipped cabinet in 20×20G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Number of shelves	1
Height	750 mm

Width	500 mm
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
ComfortClose	no
Weight	28 kg
Cabinet fronts	Viewing window swing door
Handle positioning	top
Electronic locking system can be retrofitted	yes
Usable height	595 mm
Depth	500 mm
Depth in G	20
Width in G	20
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

Accessories

Cover made of laminated wood Dimension in G 20X20	951985 20X20
Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
Storage shelf for cabinet / compartment width in G 20	940550 20
Drawer for swing-door cabinets, Width 20G Drawer front height 100 mm	940640 100
	940640 200

Drawer for swing-door cabinets,Width 20G Drawer front height 200 mm

Drawer for swing-door cabinets,Width 20G Drawer front height 300 mm

940640 300

Cover made of bamboo Dimension in G 20X20

951980 20X20

Drawer for swing-door cabinets,Width 20G Drawer front height 125 mm

940640 125

Inclined shelf for cabinet / compartment width in G 20

940560 20

Drawer for swing-door cabinets,Width 20G Drawer front height 150 mm

940640 150

Slide handle for GridLine Type GP11

914226 GP11

Basic lighting set for GridLine cabinets withswing doors for cabinet height 750/800 mm

940501 750/800

Drawer for swing-door cabinets,Width 20G Drawer front height 75 mm

940640 75

Storage shelf slotted for cabinet / compartment width in G 20

940552 20