

Garant GRIDLINE

**Base cabinet with Plain sheet metal swing doors, Height: 1000mm****Order data**

Order number	940001 1000
GTIN	4062406067021
Item class	9GI

**Description****Version:**

Equipped cabinet in 20×20G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

**Supplied with:**

Cabinet with storage shelves.

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Depth	500 mm
Cabinet fronts	Plain sheet metal swing door

Width	500 mm
Usable height	845 mm
Number of shelves	2
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Electronic locking system can be retrofitted	yes
Height	1000 mm
ComfortClose	no
Handle positioning	top
Weight	36 kg
Width in G	20
Depth in G	20
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of cabinet	Base cabinet
Type of product	Cabinet with shelves

## Accessories

Drawer for swing-door cabinets,Width 20G Drawer front height 200 mm	940640 200
Drawer for swing-door cabinets,Width 20G Drawer front height 125 mm	940640 125
Cover made of laminated wood Dimension in G 20X20	951985 20X20
	940640 300

Drawer for swing-door cabinets,Width 20G Drawer front height 300 mm

Cover made of bamboo Dimension in G 20X20	951980 20X20
---	--------------

Drawer for swing-door cabinets,Width 20G Drawer front height 100 mm

940640 100
------------

Slide handle for GridLine Type GP11

914226 GP11
-------------

Inclined shelf for cabinet / compartment width in G 20

940560 20
-----------

Drawer for swing-door cabinets,Width 20G Drawer front height 75 mm

940640 75
-----------

Storage shelf for cabinet / compartment width in G 20

940550 20
-----------

Storage shelf slotted for cabinet / compartment width in G 20

940552 20
-----------

Shelf clip set for GridLine cabinets20 pieces Type F

940559 F
----------

Basic lighting set for GridLine cabinets withswing doors for cabinet height 900/1000 mm

940501 900/1000
-----------------

Drawer for swing-door cabinets,Width 20G Drawer front height 150 mm

940640 150
------------