

Garant GRIDLINE

**Base cabinet with Plain sheet metal swing doors, Height: 750mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 940001 750    |
| GTIN         | 4062406066697 |
| Item class   | 9GI           |

**Description****Version:**

Equipped cabinet in 20×20G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

**Supplied with:**

Cabinet with storage shelves.

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

|                   |        |
|-------------------|--------|
| Number of shelves | 1      |
| Height            | 750 mm |

|   |  |
|---|--|
| Handle positioning  | top  |
| Weight  | 28 kg  |
| Electronic locking system can be retrofitted                    | yes  |
| Cabinet fronts  | Plain sheet metal swing door                                   |
| Depth   | 500 mm   |
| Shelf load capacity / maximum distributed shelf load (on metal) | 100 kg   |
| ComfortClose  | no   |
| Usable height   | 595 mm   |
| Width   | 500 mm   |
| Depth in G  | 20   |
| Width in G  | 20   |
| Material thickness  | 0.9 mm   |
| Cabinet housing internal load capacity                          | 1000 kg  |
| Door opening angle  | 250 degrees  |
| Height adjustment interval                                      | 25 mm  |
| Cylinder lock   | modular barrel   |
| Colour selection  | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of cabinet   | Base cabinet   |
| Type of product   | Cabinet with shelves   |

## Accessories

|  |                |
|--|----------------|
| Drawer for swing-door cabinets,Width 20G Drawer front height 100 mm                    | 940640 100     |
| Storage shelf for cabinet / compartment width in G 20                                  | 940550 20      |
| Basic lighting set for GridLine cabinets withswing doors for cabinet height 750/800 mm | 940501 750/800 |
|  | 940640 200     |

Drawer for swing-door cabinets,Width 20G Drawer front height 200 mm

Drawer for swing-door cabinets,Width 20G Drawer front height 125 mm

940640 125

Slide handle for GridLine Type GP11

914226 GP11

Inclined shelf for cabinet / compartment width in G 20

940560 20

Drawer for swing-door cabinets,Width 20G Drawer front height 75 mm

940640 75

Shelf clip set for GridLine cabinets20 pieces Type F

940559 F

Drawer for swing-door cabinets,Width 20G Drawer front height 150 mm

940640 150

Cover made of bamboo Dimension in G 20X20

951980 20X20

Cover made of laminated wood Dimension in G 20X20

951985 20X20

Drawer for swing-door cabinets,Width 20G Drawer front height 300 mm

940640 300

Storage shelf slotted for cabinet / compartment width in G 20

940552 20