

Garant GRIDLINE

Base cabinet with Viewing window swing doors, Height: 900mm**Order data**

| | |
|--------------|---------------|
| Order number | 940003 900 |
| GTIN | 4062406067076 |
| Item class | 9GI |

Description**Version:**

Equipped cabinet in 20×20G. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** for base cabinets, with 4 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the push handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

| | |
|--------|--------|
| Width | 500 mm |
| Weight | 32 kg |

| | |
|---|--|
| ComfortClose | no |
| Handle positioning | top |
| Depth | 500 mm |
| Number of shelves | 1 |
| Shelf load capacity / maximum distributed shelf load (on metal) | 100 kg |
| Height | 900 mm |
| Cabinet fronts | Viewing window swing door |
| Electronic locking system can be retrofitted | yes |
| Usable height | 745 mm |
| Width in G | 20 |
| Depth in G | 20 |
| Material thickness | 0.9 mm |
| Cabinet housing internal load capacity | 1000 kg |
| Door opening angle | 250 degrees |
| Height adjustment interval | 25 mm |
| Cylinder lock | modular barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of cabinet | Base cabinet |
| Type of product | Cabinet with shelves |

Accessories

| | |
|---|--------------|
| Drawer for swing-door cabinets,Width 20G Drawer front height 300 mm | 940640 300 |
| Cover made of laminated wood Dimension in G 20X20 | 951985 20X20 |
| Slide handle for GridLine Type GP11 | 914226 GP11 |
| Inclined shelf for cabinet / compartment width in G 20 | 940560 20 |
| | 940640 150 |

Drawer for swing-door cabinets,Width 20G Drawer front height 150 mm

Drawer for swing-door cabinets,Width 20G Drawer front height 75 mm

940640 75

Basic lighting set for GridLine cabinets withswing doors for cabinet height 900/1000 mm

940501 900/1000

Storage shelf slotted for cabinet / compartment width in G 20

940552 20

Drawer for swing-door cabinets,Width 20G Drawer front height 125 mm

940640 125

Drawer for swing-door cabinets,Width 20G Drawer front height 200 mm

940640 200

Shelf clip set for GridLine cabinets20 pieces Type F

940559 F

Storage shelf for cabinet / compartment width in G 20

940550 20

Cover made of bamboo Dimension in G 20X20

951980 20X20

Drawer for swing-door cabinets,Width 20G Drawer front height 100 mm

940640 100